



Counting chambers Zwerver



TECHNICAL DATA

Material	Plexiglass, glass, stainless steel
Dimensions of emptying chassis	56 x 120 mm
Inner diameter of sedimentation cylinder	24 mm
Dimensions of the chamber	plastic: 50 x 56 metal ring diameter = 44 mm
Height of sedimentation cylinders	10 ml = 17 mm 25 ml = 50 mm
Bottom glass	thickness = 0,17 mm diameter = 35 mm



Cleaning:
Normally just rinse with water.

From time to time a gentle wash with a soft brush and detergent.

**DON'T USE
HOT WATER
OR
ALCOHOL.**

How to use?
See videos for filling:

<https://www.youtube.com/watch?v=lsWVL-Tmdfw>

emptying:

<https://www.youtube.com/watch?v=cd6sJ2TY3M0>

The product is protected by the Finnish utility model 9888.

Company Zwerver
Kuninkaanmäentie 65
FIN-25700 Kemiö
FINLAND
www.zwerver.fi
info@zwerver.fi
+358-(0)40- 707 9385

VAT number: FI15347541